



ASPHERIC COEFFICIENTS

	R	k	A ₂	A ₄	A ₆	A ₈	A ₁₀
S1	632.73	-	-	-	-	-	-
S2	-5.48	-	-	5.0928987E-04	1.2863102E-06	8.7003479E-07	-

$$z = \frac{Y^2}{R(1 + \sqrt{1 - (1+k)Y^2/R^2})} + A_2Y^2 + A_4Y^4 + A_6Y^6 + A_8Y^8 + A_{10}Y^{10}$$

ASPHERIC LENS EQUATION



ISOMETRIC VIEW
1 : 1

NOTES/SPECIFICATIONS:

- DESIGN WAVELENGTH: 780nm
- EFFECTIVE FOCAL LENGTH: 8.00mm
- EFL TOLERANCE: ±1%
- NUMERICAL APERTURE: 0.50
- WORKING DISTANCE: 5.92mm
- DIAMETER TOLERANCE: ±0.015mm
- CENTER THICKNESS TOLERANCE: ±0.04mm
- LASER WINDOW THICKNESS: 0.25mm (N-BK7)
- SURFACE QUALITY: 60-40 SCRATCH-DIG (INCLUDES ENTIRE BULK MATERIAL)
- RMS WFE(TYPICAL): 0.058 WAVES
- MAGNIFICATION: INFINITE
- REFRACTIVE INDEX (AT DESIGN WAVELENGTH): 1.680
- COATING(S1 & S2): BBAR Ravg<0.5% FROM 350-700nm

FOR INFORMATION ONLY
NOT FOR MANUFACTURING PURPOSES

DRAWING PROJECTION			THORLABS www.thorlabs.com	
NAME	DATE	-A COATED ASPHERIC COLLIMATING LENS EFL=8.00mm		
DRAWN	21/DEC/10	MATERIAL		REV
APPROVAL	25/MAR/13	D-LAK6		G
COPYRIGHT © 2010 BY THORLABS		ITEM #	APPROX WEIGHT	
VALUES IN PARENTHESIS ARE CALCULATED AND MAY CONTAIN ROUND OFF ERRORS		A240-A	0.1g	